

Body Shape RF

The Safe Method for Body Contouring

BODY SHAPE RF is an innovative product, designed to achieve:

- Skin Rejuvenation
- Body Contouring
- Skin Lifting
- Cellulite Improvement

INNOVATIVE TECHNOLOGY:

- **Temperature Sensors** integrated in the Applicators for continuous skin-temperature monitoring, assuring effective and problem free treatments
- **Computerized Spike Control System** Ensures safe and painless treatment
- **Switch and Pedal Free Operation**
- **Quadro & Bi-Polar Applicators:** Large working surface, with exact layer and deep tissue targeting
- **High Power** (up to 250 Watt) enabling a powerful treatment with the best possible results

**Amazing Results
Affordable Price !**

**On-Line Skin
Temperature
Measurement**



Body Shape RF

The Safe Method for Body Contouring

Bi-Polar

Temp. Controlled
Facial Applicator





Quadro-Polar

Temp. Controlled
Body Applicator



• Deep Energy •
Penetration



Physiological Process

Twisted & unresponsive
Collagen Fibers


Visible Wrinkle

Sorted & supportive
Collagen Fibers

Flattened Wrinkle



Excessive layer of
Enlarged Fat Cells




Reduced layer of
Normal Fat Cells

Body Shape RF


The Safe Method for Body Contouring

CSCS – Computerized Spike Control System

CSCS monitors a uniform flow of energy by measuring each RF pulse and by trimming unwanted Energy Spikes. It ensures safe and painless treatments, with optimal adjustment to the individual Skin Impedance.



Before




After 3 Treat.



Body Shape RF

The Safe Method for Body Contouring



3 Simple Steps Operation:

- a. Set the Time Duration
- b. Set the recommended Energy
- c. Set the targeted Skin Temperature

Before



After



Before



After



MAXIMUM OUTPUT	250 WATT
FREQUENCY	6.8 MHZ
APPLICATORS	BODY QUADRO POLAR FACIAL BI-POLAR
TEMPERATURE SENSOR	INFRA-RED HI-SPEED INTEGRATED TEMPERATURE SENSOR IN EACH APPLICATOR
EMERGENCY HALTING	PATIENT'S EMERGENCY HALTING KNOB
MAINS	220-230VAC 50/60Hz 100-120VAC 50/60Hz
MAX MAINS POWER	600 VA